



**TECNOSERVICE'21 srl**

by Tinti Sergio  
Via Carlo Pisacane, 134  
61032 Fano (PU) Italy  
P.IVA IT0200411413

Tel. +39 0721 805911  
FAX +39 0721 809794  
e-mail: [staff@technochef.it](mailto:staff@technochef.it)  
[www.technochef.it](http://www.technochef.it)  
[www.technochef.eu](http://www.technochef.eu)

Services and Technologies for professional catering since 1973



#### TECHNICAL CARD

|                                  |          |
|----------------------------------|----------|
| <b>power supply</b>              | Monofase |
| <b>Volts</b>                     | V 230/1  |
| <b>frequency (Hz)</b>            | 50       |
| <b>motor power capacity (Kw)</b> | 0,5      |
| <b>net weight (Kg)</b>           | 20       |
| <b>breadth (mm)</b>              | 260      |
| <b>depth (mm)</b>                | 300      |
| <b>height (mm)</b>               | 500      |

#### PROFESSIONAL DESCRIPTION

##### **MANUAL benchtop heat sealer for TRAYS, without MOLDS:**

- made **for packaging in PREFORMED TRAYS** with a **MAXIMUM measurement of 205x150x100h mm** seal with **transparent FILM**;
- Made of **stainless steel** and **anodized aluminium** ;
- **Teflon-coated aluminum sealing plate** with **electronic temperature control (0°-200°)**;
- **Nine storable welding PROGRAMS**;
- Acoustic and **luminous warning** at the end of the cycle;
- **Motorized automatic welding**, powered solely by electricity;
- The **welding cycle is automatically activated when the mold is fully inserted**;
- **The closing film is automatically dragged** by inserting the mold into the machine and is subsequently **automatically cut at the end of the sealing cycle** ;
- Maximum **film reel dimensions** : length **150 mm** - diameter **160 mm** .



##### **OPERATION'**

- Insert the tray into the mold placed on the guides,
- Push the mold **FULLY** towards the machine holding the athermal handle,
- Start the welding cycle by manually acting on the appropriate lever,
- At the sound of the BEEP you can extract the mold and remove the tray.

##### **OPTIONAL - ACCESSORIES :**

- **INFINITY mould, ADJUSTABLE** for trays, patented, **ADAPTABLE with 3 second operation** , to **12 different SIZES**;
- On request: **Design of molds** for customized trays;
- **Carter Protect Film**;
- **Micro-Perforator group for film** , (necessary when you want to package very hot products that emit a lot of steam);

**CE mark**  
**Made in Italy**

| CODE  | DESCRIPTION   | PRICE/DELIVERY |
|---|---|----------------|
| <b>JP-TSM101-R</b>  | MANUAL LEVER THERMO SEALER WITHOUT MOLD, for PREFORMED TRAYS with MAX MEASUREMENT of mm 205x150x100h, V.230/1, kw 0.5, dimensions mm 260x300x500h |                |
| <b>TECHNICAL CARD</b>   |   |                |
| CODE/PICTURES   | DESCRIPTION   | PRICE/DELIVERY |
| <b>JP-DA000098</b><br> | <b>Drilling Group</b>   |                |
| <b>JP-DS0137</b><br>   | <b>Technochef - INFINITY 1 MOLD for Thermosealers mod.TSM101-R and TSS101-R</b>   |                |